SELECTION GUIDE

It is crucial to get the glove size right for maximum dexterity.

Here are a few recommendations to help you in finding
the right size of gloves you need.

Glove size	Hand (mm)		Glove (mm)
further to EN420	Palm circumference	Length	Minimum length
6	152	160	220
7	178	171	230
8	203	182	240
9	229	192	250
10	254	204	260
11	279	215	270

Color-coded Cuff

Some styles of Showa Best Glove have a color-coded cuff. These cuffs enable the size recognition in the factory and the pairing after washing the gloves.

Testing Prior To Using

If he over is too small, it cuts off the blood circulation and restricts the movement of the hand. On the contrary, too big gloves slip off at the slightest movement and make your handling very imprecise. To be sure of your size and fit don't hesitate to ask for samples from your Showa Best Glove distributor.

7 8 9 10 11

Place your right hand on the diagram: the blue line should be be tween your thumb and index finger. The size is indicated on the right.